








RoHS Compliant



公母对插后尺寸



备注:

1. 材质及电镀: 见图

2. 电气性能:  
2.1 接触电阻: 30mΩ Max FOR INITIAL  
40mΩ Max AFTER TEST

2.2 耐电压: 100V AC


2.3 绝缘:  $100\text{M}\Omega$  Min

2.4 额定电流，

2.4 供应电源：  
COLLECTIVELY VBUS PIN (A4,A9,B4,B9) ,TOTAL 5A  
VCCON PIN (B5) THROUGH GND PIN(A1,A12,B1,B12),1.25A  
OTHERS PIN, 0.25A

2.5 工作温度:  $-40^{\circ}\text{C} \sim 80^{\circ}\text{C}$

- 3. 机械性能:
    - 3.1 插入力: 5~20N.
    - 3.2 拔出力: 初始值8~20N 测试后6~20N
    - 3.3 寿命: 10,000 CYCLES



07	外壳	不锈钢	1	SUS 304 1/2H,TO.30
06	二次Molding件	LCP	1	黑色 UL94 V-0
05	Molding件2	LCP	1	黑色 UL94 V-0
04	Molding件1	LCP	1	黑色 UL94 V-0
03	中夹片	SUS301-H T=0.15	1	不电镀
01	端子	C2680-H T=0.15	1set	功能接触触点镀金，脚端镀金

 联晟欣连接器（深圳）有限公司  
Lianshenxin Connector (Shenzhen) Co., Ltd

INTERSECTION POINT (IP)		DESIGN	Andy	DATE	2014.12.24	TITLE: TYPE C 16PIN单排卧式7.35mm 母座 黄铜		
UNLESS OTHERWISE SPECIFIED,TOLERANCE:		CHECKED		DATE				
X.	±0.25	APPROVED		DATE				
X.x	±0.20	PART NO: LCK-TCF831-L735YL-G1			REV: 04	SCALE: 1:1	UNIT: mm	
X.xx	±0.15	DRAWING NO:			SIZE: A4	SHEET: 1/1		
ANGULAR								
±3°								