





HSF



ROHS



NOTES:

1. MATERIAL: PHOSPHOR BRONZE, T=0.25mm.

2. PLATING:

80U" Min NICKEL PLATED OVERALL

50U" Min NICKEL PLATED UNDER OVERALL

3. THIS PRODUCT IS SUITABLE FOR 20mm PC COIN CELL CLIP

Order Code:

BS - S - SI - R - 3003B
① ② ③ ④ ⑤

① BS: Battery Contacts

② Apperance For The Product
S:180 TYPE

③ Contact Plating

SI:Nickel Plate

SN:Tin

G0:Gold flash

G1: 3U" Gold

G2: 5U" Gold

G3:10U" Gold

G4:15U" Gold

G5:30U" Gold

④ Packing Method

A: Bag Packing

R: Tape & Reel Packing

⑤ Product Number

3003B

Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15SCALE:
As ShownUNIT:
mmDRAW
Wu Feng RongDATE
12/11/2020CHECK
BobYangDATE
12/11/2020

TITLE:

E-

mail:sales@antenk.com
BATTERY CONTACTS FOR 3003B, STRAIGHT LEGS

DRAWING NO: BS-S-SI-R-3003B

PRODUCT NO: BS-S-SI-R-3003B



3rd ANGLE PROJECTION



REV

0.4 Change 0.6+/-0.2

08/03/2022

DESCRIPTION

DATE