






3.1 工作温度: $-30^{\circ}\text{C} \sim +85^{\circ}\text{C}$

PIN	NUMBER	SIGNAL NAME
A1		GND
A2		SSTXp1
A3		SSTXn1
A4		VBUS
A5		CC1
A6		Dp1
A7		Dn1
A8		SBU1
A9		VBUS
A10		SSRXn2
A11		SSRXp2
A12		GND



TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 母座24P 沉板前插后贴 L=10.0	
CHECKED BY: 马跃				DATE : 2014-02-23	PART NO. HYCW641-USBC24-1000B
 UNIT: mm [inch]		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2512111612
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1