

1

2


3

4

5





REV.	ECN	DESCRIPTION	MDF'D	DATE
		新订图面		

双头同向10064#32红黑线100mm



参数:

1. 线数: 20~30
2. 适用线规: AWG32#
3. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
4. 额定电压/电流: 30V/DC 0.35A
5. 接触电阻: $\leq 50\text{m}\Omega$
6. 绝缘电阻: $> 100\text{M}\Omega$
7. 耐压: 500V AC/60s
8. 胶壳材质: LCP, UL94V-0



Applicable Wire: AWG#32

Mated Condition

Circuits	A	B	C	Circuits	A	B	C
02P	0.80	1.78	2.40	12P	8.80	9.78	10.40
03P	1.60	2.58	3.20	13P	9.60	10.58	11.20
04P	2.40	3.38	4.00	14P	10.40	11.38	12.00
05P	3.20	4.18	4.80	15P	11.20	12.18	12.80
06P	4.00	4.98	5.60	16P	12.00	12.98	13.60
07P	4.80	5.78	6.40	17P	12.80	13.78	14.40
08P	5.60	6.58	7.20	18P	13.60	14.58	15.20
09P	6.40	7.38	8.00	19P	14.40	15.38	16.00
10P	7.20	8.18	8.80	20P	15.20	16.18	16.80
11P	8.00	8.98	9.60				



深圳市韩下电子有限公司

品名 (ITEM NO)	HX 0.8-2P ST 100mm 32AWG
料号 (PART NO)	
图号 (DWG NO)	

页码 (SHEET)	1	单位 (UNIT): MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2025.12.10	未注公差 TOLERANCE UNSPECIFIED
设计 (DESIGN)	黄彬	> XX ±3
审核 (CHECKED)	张伟	> X ±1
核准 (APPROVED)	罗小春	0.X ±0.20
		0.XX ±0.15