




3D VIEW

RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)
RECOMMENDED MATAL MASK T=0.12mm

/// SMT SOLDER AREA
/// NO PATTERN AND VIA HOLE IN HTIS AREA

NOTES:

1.MATERIAL:

HOUSING: High Temperature Thermoplastic

Terminal:Copper Alloy

Shell: Stainless Steel

2.PLATING:

Terminal:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

Shell:30u" Ni UNDERPLATED OVERALL

G/F PLATED ON CONTACT AREA AND SOLDER AREA

3.technical speciality:

RATED VOLTAGE: 30V AC MAX.

CURRENT RATING: 0.5A MAX.


INSULATION RESISTANCE:1000MΩ MIN

CONTACT REISTANCE:100mΩ MAX

WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTES

OPERATING TEMPERATURE: -40℃~+85℃Humidity 80% R.H MAX

4.DIMENSIONS WITH MARK * "MUST BE MEASURE BY QC AND IPQC



PIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
CD	Detect Switch
C5	GND
C6	VPP
C7	I/O


DIMENSION IN mm	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X±0.3	X.*±3
.XX±0.2	.X.*±2
.XXX±0.1	.XX.*±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyecom Electronics Co.,Ltd

APR.	Alex	TITLE:	1.37H NANO SIM CARD CONNECTOR(L) 规格
CHK.	Jack	DWG NO.	XY-NANO-113
DRA.	Can	PROJ.	CUSTOMER DRAWING
SIZE	A4	SCALE	1:1
SHEET	1/1	REV.	A

NOTES

1. NUMBER OF CONNECTORS:1500PCS/REEL
2. LEAD TAPE LENGTH





3. QUANTITY:15000PCS/CARTON

4. WEIGHT :

3.1 NET WEIGHT : Kg

3.2 GROSS WEIGHT : Kg



DIMENSION IN mm		厦门市辛译精密电子有限公司					
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyconn Electronics Co.,Ltd					
.X±0.3	X.*±3	APR.	Alex	TITLE: 1.37H NANO SIM CARD CONNECTOR(1.37) 规格			
.XX±0.2	.X*±2	CHK.	Jack	DWG NO. XY-NANO-113			
.XXX±0.1	.XX*±			PROJ. 	CUSTOMER DRAWING		
		DRA.	Can	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A