

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy



ELECTRICAL:

Current rating: 2 Amps .

Contact resistance: 20 m Ω initialInsulation resistance: 1000 M Ω min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



Pitch	Position	Rows with Contacts	Contact Arrange
2.54	96	A B C	
	64	A - C	
	32	A - -	
5.08	48	A B C	
	32	A - C	
	16	A - -	

PCB LAYOUT(RECOMMENDED)

(TOP VIEW TOL. :±0.05)

9001- 1 4 64 1 C 00 A
Series 1:2.54mm 4:Female Position 1:Dip Length C:Selective 00:G/F A:Tray
2:5.08mm Gold Plated Package

公差一览表 TOLERANCE UNLESS OTHERWISE			
X.	±0.25	X°.	±5°
.X	±0.20	.X°.	±2°
.XX	±0.15	.XX°.	±1°
.XXX	±0.02	.XXX°.	±0.5°
日期 Date	2009. 04. 15		



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE	欧式插座 DIN41612
角法 VIEW		设计 DESIGN	LZG	364弯孔	90度母座
比例 SCALE	1:1	审核 CHKD	FGD	产品料号 PART NO.	LXW254-364-WK-G
版本 VER	A0	核准 APPD	ZY	图号 DRAW NO.	9001-14641C00A-A0