






NOTES:

- 1.HUOSING:LCP HGH-TEMP
THERMOPLASTIC UL94V-0
- 2.TERMINAL:PHOSPHOR BRONZE
- 3.COLOR:BEIGE



SOCKET H1	MATED HEIGHT PLUG H			
	4.70	5.70	6.70	7.70
3.70	5.00	6.00	7.00	8.00
7.70	9.00	10.00	11.00	12.00
11.70	13.00	14.00	15.00	16.00
15.70	17.00	18.00	19.00	20.00

Model	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
XY-400S-DF85C	40	21.80	15.20	16.80	20.20	18.80	20.15
XY-500S-DF85C	50	25.80	19.20	20.80	24.20	22.80	24.15
XY-600S-DF85C	60	29.80	23.20	24.80	28.20	26.80	28.15
XY-800S-DF85C	80	37.80	31.20	32.80	36.20	34.80	36.15
XY-1000S-DF85C	100	45.80	39.20	40.80	44.20	42.80	44.15
XY-1200S-DF85C	120	53.80	47.20	48.80	52.20	50.80	52.15
XY-1400S-DF85C	140	61.80	55.20	56.80	60.20	58.80	60.15
XY-1600S-DF85C	160	69.80	63.20	64.80	68.20	66.80	68.15
XY-1800S-DF85C	180	77.80	71.20	72.80	76.20	74.80	76.15
XY-2000S-DF85C	200	85.80	79.20	80.80	84.20	82.80	84.15

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 0.8mm PITCH BTB CONNECTOR SOCKET			
.X±0.35	X.*±1	APR.	Alex	DWG NO. XY-NDS-DF85C	
.XX±0.25	.X.*±	CHK.	Jack	PROJ.  CUSTOMER DRAWING	
.XXX±0.1	.XX.*±	DRA.	Can	SIZE A4	SCALE 1:1
		SHEET 1/1		REV.	A