







ROHS



PCB LAYOUT MOUNTING PATTERN



SCHEMATIC



SPECIFICATIONS

Rating	DC 12V 50mA
Contact Resistance	100mΩ Max.
Travel	0.3 ± 0.1mm
Operating Force	75gf ± 5gf
Operating Life(cycles)	100,000

5	HSa6.0428.047-5	按钮	1	PPA
4	HSa6.0428.018-4	按垫	1	橡胶
3	HSa6.0428.030-3	盖板	1	PPA(黑)
2	HSa6.0428.005-2	簧片	1	不锈钢复银
1	HSa6.0428.025-1	底座组	1	PPA(黑) 黄铜带H65Y0.3mm
序号	编号	材料	数量	材料

The material contained in this drawing is the property of XiBang. Any use other than that specifically authorized by XiBang is prohibited. The above drawing IS subjected to change for improvement without prior notice.

 Switch Connector		东莞市溪榜电子有限公司 DONG GUAN XI BANG ELECTRONICS CO.,LTD										
		TITLE : XB TACT SWITCH						8	REEL	PS	1	BLUE
		MODEL : XB-TS-4DV050 贴片开关带柱 贴片轻触开关6.2x6.2x5mm						7	CARRIER	PS	1	CLEAR
UNIT : MM		DWN.		DATE			6	COVER TAPE	PS	1	CLEAR	
SCALE : 5 : 1		CHK'D		DATE		TOLERANCE ≤1.5mm ± 0.1 > 1.5mm ± 0.2 ≥10.0mm ± 0.3	ANGLE TOL ± 2°	5	CONTACT	PBS STRIP	1	Ag CLAD
VERSION		APPD.		DATE				4	COVER	IRON STRIP	1	Ni PLATED
01								3	CASE	NYLON	1	BLACK
								2	TERMINAL	BRASS STRIP	2	Ag PLATED
								1	KNOB	NYLON	1	BLACK
								NO.	PART NAME	MATERIAL	QTY.	FINISHING