





REV.	Q'TY	ECN. NO.	APR.	DATE



SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40°to+105°  
 Contact Material: Brass  
 Insulator Material: Polyester(UL 94V-0)  
 Contact plating: Gold Flash  
 Standard: PA6T  
 Max.Processing Temp: 240°C for30-60seconds  
 (260°Cfor10seconds)

P/N	PIN	DIM.A	DIM.B
XY-IDC2.54-2*03P-LT	2*3	5.08	7.62
XY-IDC2.54-2*04P-LT	2*4	7.62	10.16
XY-IDC2.54-2*05P-LT	2*5	10.16	12.70
XY-IDC2.54-2*06P-LT	2*6	12.70	15.24
XY-IDC2.54-2*07P-LT	2*7	15.24	17.78
XY-IDC2.54-2*08P-LT	2*8	17.78	20.32
XY-IDC2.54-2*09P-LT	2*9	20.32	22.86
XY-IDC2.54-2*10P-LT	2*10	22.86	25.40
XY-IDC2.54-2*12P-LT	2*12	27.94	30.48
XY-IDC2.54-2*13P-LT	2*13	30.48	33.02
XY-IDC2.54-2*14P-LT	2*14	33.02	35.56
XY-IDC2.54-2*15P-LT	2*15	35.56	38.10
XY-IDC2.54-2*16P-LT	2*16	38.10	40.64
XY-IDC2.54-2*17P-LT	2*17	40.64	43.18
XY-IDC2.54-2*18P-LT	2*18	43.18	45.72
XY-IDC2.54-2*20P-LT	2*20	48.26	50.80
XY-IDC2.54-2*22P-LT	2*22	53.34	55.88
XY-IDC2.54-2*25P-LT	2*25	60.96	63.50
XY-IDC2.54-2*30P-LT	2*30	73.66	76.20
XY-IDC2.54-2*32P-LT	2*32	78.74	81.28



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54DC3-NPIn H8.9 SMT PC10.2 PB9.6 L11.5 6T
.X±0.3	X.*± 5'	CHK.	Jack	DWG NO. XY-IDC2.54-2*NP-LT
.XX±0.2	.X.*± 1	DRA.	Can	PROJ.  CUSTOMER DRAWING
.XXX±0.1	.XX.*± 0.5	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A