





REV.	Q'TY	ECN. NO.	APR.	DATE



SPECIFICATIONS
 Current Rating: 3Amps
 Insulation Resistance: 1000MQ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insrlator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PM254-1-01P-W-8.5	1	0.00	2.54
XY-PM254-1-02P-W-8.5	2	2.54	5.08
XY-PM254-1-03P-W-8.5	3	5.08	7.62
XY-PM254-1-04P-W-8.5	4	7.62	10.16
XY-PM254-1-05P-W-8.5	5	10.16	12.70
XY-PM254-1-06P-W-8.5	6	12.70	15.24
XY-PM254-1-07P-W-8.5	7	15.24	17.78
XY-PM254-1-08P-W-8.5	8	17.78	20.32
XY-PM254-1-09P-W-8.5	9	20.32	22.86
.....
XY-PM254-1-40P-W-8.5	40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54FH H8.5 1xnPin 90度 Y型 PC3.2 PB10.2 6T
.X±0.3	X.*± 5'	CHK.	Jack	DWG NO. XY-PM254-1-NP-W-8.5
.XX±0.2	.X*± 1	DRA.	Can	PROJ. CUSTOMER DRAWING
.XXX±0.1	.XX*± 0.5	SIZE	A4	SCALE 1:1 SHEET 1/1 REV. A