

**SPECIFICATION**

**MATERIAL:**

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

**ELECTRICAL:**





Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)  
(TOP VIEW TOL. :±0.05)

Length	1	2	W1	W2	W3
L	4.0	2.5	13	15	17
Pitch	Position	Rows with Contacts	Contact Arrange		
2.54	32	A B			
	16	A -			
5.08	16	A B			
	8	A -			

9001- 3 6 32 1 C 00 A  
 Series 3:2.54mm 6:Female Position 1:Dip Length C:Selective 00:G/F A:Tray  
 2:5.08mm W1:Dip Length Gold Plated Package  
 W2:Dip Length

公差一览表 TOLERANCE UNLESS OTHERWISE				LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD							
X.	±0.25	X°	±5°	单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE	欧式插座 DIN41612 232直孔 180度母座		
.X	±0.20	.X°	±2°	角法 VIEW		设计 DESIGN	LZG				
.XX	±0.15	.XX°	±1°	比例 SCALE	1:1	审核 CHKD	FGD	产品料号 PART NO.	LXW254-232-ZK-G		
.XXX	±0.02	.XXX°	±0.5°	日期 Date	2009.04.15	版本 VER	A0	核准 APPD	ZY	图号 DRAW NO.	9001-36321C00A-A0