

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:





Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)

(TOP VIEW TOL. :±0.05)

Pitch	Position	Rows with Contacts	Contact Arrange
2.54	30	A B C	
	20	A - C	
	10	A - -	
5.08	15	A B C	
	10	A - C	
	5	A - -	

9001-

1

8

30

1

C

00

A

Series

1:2.54mm
2:5.08mm

8:Female

Position

1:Dip Length

C:Selective
Gold Plated

00:G/F

A:Tray
Package

公差一览表
TOLERANCE UNLESS OTHERWISE

X.	±0.25	X°.	±5°
.X	±0.20	.X°	±2°
.XX	±0.15	.XX°	±1°
.XXX	±0.02	.XXX°	±0.5°
日期 Date	2009. 04. 15		



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE	欧式插座 DIN41612 330弯孔 90度母座
角法 VIEW		设计 DESIGN	LZG	产品料号 PART NO.	LXW254-330-WK-G
比例 SCALE	1:1	审核 CHKD	FGD	图号 DRAW NO.	9001-18301C00A-A0
版本 VER	A0	核准 APPD	ZY		