






REV.	Q'TY	ECN. NO.	APR.	DATE



Electrical
 Voltage:50 V AC(rms)/DC
 Current:0.5A AC(rms)/DC
 Contact Resistance:40 mΩ max(initial)
 Dielectric withstanding Voltage:200 V Ac/rms
 Insulation Resistance:500 MΩ min
 Operating Temp:-25°C +85°C

MATERIAL:
 HOUSING:LCP NATURE(UL94V-0)
 TERMINAL:PHOSPHOR BRONZE C5191R-H



RECOMMENDED PCB PATTERN DIM.
 TOLERANCE : ±0.05

Model	PIN	DIM A	DIM B	DIM C
XY-10DS-DF520C	10	5.60	3.50	2.00
XY-12DS-DF520C	12	6.10	4.00	2.50
XY-14DS-DF520C	14	6.60	4.50	3.00
XY-16DS-DF520C	16	7.10	5.00	3.50
XY-18DS-DF520C	18	7.60	5.50	4.00
XY-20DS-DF520C	20	8.10	6.00	4.50
XY-22DS-DF520C	22	8.60	6.50	5.00
XY-24DS-DF520C	24	9.10	7.00	5.50
XY-26DS-DF520C	26	9.60	7.50	6.00
XY-28DS-DF520C	28	10.10	8.00	6.50
XY-30DS-DF520C	30	10.60	8.50	7.00
XY-32DS-DF520C	32	11.10	9.00	7.50
XY-34DS-DF520C	34	11.60	9.50	8.00
XY-36DS-DF520C	36	12.10	10.00	8.50
XY-38DS-DF520C	38	12.60	10.50	9.00
XY-40DS-DF520C	40	13.10	11.00	9.50
XY-42DS-DF520C	42	13.60	11.50	10.00
XY-44DS-DF520C	44	14.10	12.00	10.50
XY-46DS-DF520C	46	14.60	12.50	11.00
XY-48DS-DF520C	48	15.10	13.00	11.50
XY-50DS-DF520C	50	15.60	13.50	12.00
XY-52DS-DF520C	52	16.10	14.00	12.50
XY-54DS-DF520C	54	16.60	14.50	13.00
XY-56DS-DF520C	56	17.10	15.00	13.50
XY-58DS-DF520C	58	17.60	15.50	14.00
XY-60DS-DF520C	60	18.10	16.00	14.50
XY-62DS-DF520C	62	18.60	16.50	15.00
XY-64DS-DF520C	64	19.10	17.00	15.50
XY-66DS-DF520C	66	19.60	17.50	16.00
XY-68DS-DF520C	68	20.10	18.00	16.50
XY-70DS-DF520C	70	20.60	18.50	17.00
XY-72DS-DF520C	72	21.10	19.00	17.50
XY-74DS-DF520C	74	21.60	19.50	18.00
XY-76DS-DF520C	76	22.10	20.00	18.50
XY-78DS-DF520C	78	22.60	20.50	19.00
XY-80DS-DF520C	80	23.10	21.00	19.50

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR. Alex	TITLE: 0.5mm 针座		
.X±0.3	X.*±2	CHK. Jack	DWG NO. XY-NDS-DF520C		
.XX±0.2	.X*±	DRA. Can	PROJ. CUSTOMER DRAWING		
.XXX±0.1	.XX*±	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A