

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:





Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

Pitch	Position	Rows with Contacts	Contact Arrange
2.54	32	A B	
	16	A -	
5.08	16	A B	
	8	A -	

9001- 3 8 32 1 C 00 A
Series 3:2.54mm 8:Female Position 1:Dip Length C:Selective 00:G/F A:Tray
2:5.08mm Gold Plated Package

公差一览表 TOLERANCE UNLESS OTHERWISE				LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD					
X.	±0.25	X°.	±5°	单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE	欧式插座 DIN41612
.X	±0.20	.X°	±2°	角法 VIEW		设计 DESIGN	LZG	232弯孔 90度母座	
.XX	±0.15	.XX°	±1°	比例 SCALE	1:1	审核 CHKD	FGD	产品料号 PART NO.	LXW254-232-WK-G
.XXX	±0.02	.XXX°	±0.5°	日期 Date	2009.04.15	版本 VER	A0	核准 APPD	ZY
								图号 DRAW NO.	9001-38321C00A-A0