







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
XY-PM254-2-01P-Z-8.5	2*1	0.00	2.54
XY-PM254-2-02P-Z-8.5	2*2	2.54	5.08
XY-PM254-2-03P-Z-8.5	2*3	5.08	7.62
XY-PM254-2-04P-Z-8.5	2*4	7.62	10.16
XY-PM254-2-05P-Z-8.5	2*5	10.16	12.70
XY-PM254-2-06P-Z-8.5	2*6	12.70	15.24
XY-PM254-2-07P-Z-8.5	2*7	15.24	17.78
XY-PM254-2-08P-Z-8.5	2*8	17.78	20.32
XY-PM254-2-09P-Z-8.5	2*9	20.32	22.86
.....			
XY-PM254-2-40P-Z-8.5	2*40	(PIN-1)X2.54	(PIN)X2.54

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	X.*± 5°	APR. Alex	TITLE: 2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T		
.XX±0.2	.X*± 1	CHK. Jack	DWG NO. XY-PM254-2-NP-Z-8.5		
.XXX±0.1	.XX*± 0.5	DRA. Can	PROJ. 	CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1