






- MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

- SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C ~ +105° C.

* 【胶壳颜色、防火要求、环保要求及电镀规格 依客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)

PCB TOLERANCE: ±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: DR9MX#	
.X±0.35	.X*±5°	CHK.	Jack	DWG NO. XYDMR009-PM	
.XX±0.25	.X*±3°	DRA	Can	PROJ.	CUSTOMER DRAWING
.XXX±0.15	.XX*±1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A