





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ254R-12-01P	2*1	0.00	2.54
XY-PZ254R-12-02P	2*2	2.54	5.08
XY-PZ254R-12-03P	2*3	5.08	7.62
XY-PZ254R-12-04P	2*4	7.62	10.16
XY-PZ254R-12-05P	2*5	10.16	12.70
XY-PZ254R-12-06P	2*6	12.70	15.24
XY-PZ254R-12-07P	2*7	15.24	17.78
XY-PZ254R-12-08P	2*8	17.78	20.32
XY-PZ254R-12-09P	2*9	20.32	22.86
.....			
XY-PZ254R-12-40P	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 2xnPin 90° PC3.0 PA6.0 PB6.9 L13.8/18.8 6T 特種	
.X±0.35	X.*± 5°	CHK.	Jack	DWG NO. XY-PZ254R-12-NP	
.XX±0.2	.X.*± 1	DRA.	Can	PROJ.	CUSTOMER DRAWING
.XXX±0.1	.XX.*± 0.5			SIZE A4	SCALE 1:1
		SHEET	1/1	REV.	A