





NOTES:

1.MATERIAL:

- 1.1 Housing:High Temperature Thermoplastic
UL94V-0; Color Black.
- 1.2 Terminal:Copper Alloy,T=0.12mm.
- 1.3 Shell:Stainless Steel,T=0.20mm.


2.FINISH:

- 2.1 Terminal:Plated Gold on The Contact Area
and Solder Tails
- 2.2 Peg:Plated Gold on the bottom of the Solder Tails,
Tin Plated over all.

3.SPECIALITY:

- 3.1 Rated current:0.5A
- 3.2 Rated voltage:50V
- 3.3 Contact Resistance:80mΩMAX
- 3.4 Insulation Resistance:100MΩMIN 100V DC
- 3.5 Dielectric withstanding voltage: 100V AC.
- 3.6 Solder ability:245±5°C,5±0.5s.
- 3.7 Operating condition:Temperature: -40°C~+85°C
Humidity: 80% R.H MAX

NANO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A



PAD AREA


KEEP OUT AREA

③	TERMINAL	6	C5210-EH,T=0.12	G/F PLATING
②	BASE INSULATOR	1	LCP+GF30%	BLACK
①	SHELL	1	SUS304-H,T=0.15	AU/Ni PLATING
NO.	PART NAME	Q'TY	DESCRIPTION	NOTE

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 6PIN 1.4H HINGE NANO SIM CARD CONN.		
.X±0.5	X.*± 2	APR. Alex	DWG NO. NANO SIM 6Pin 1.45h	
.XX±0.2	.X.*± 1	CHK. Jack	PROJ. CUSTOMER DRAWING	
.XXX±0.1	.XX.*±	DRA. Can	SIZE A4	SCALE 1:1
			SHEET 1/1	REV. A

NOTES

1. NUMBER OF CONNECTORS:1500PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 15000PCS/CARTON

上下各1PCS珍珠棉

胶纸工字型封箱

CARTON
350*350*340 K=K

LABEL

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 6PIN 1.4H HINGE NANO SIM CARD CONN.	
.X±0.5	X.*± 2	CHK.	Jack	DWG NO. NANO SIM 6Pin 1.45h	
.XX±0.2	.X.*± 1	PROJ.	Can	CUSTOMER DRAWING	
.XXX±0.1	.XX.*±	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A