









4~34P(6.70)
35~60P(7.3)

SECTION A-A



适用扁平线(Applicable Flat Cable)

Part No	Pin	A	B	C	D
XY-FPC-05-CT-4RLTAG	4	1.50	2.56	7.60	5.20
XY-FPC-05-CT-5RLTAG	5	2.00	3.06	8.10	
XY-FPC-05-CT-6RLTAG	6	2.50	3.56	8.60	
XY-FPC-05-CT-7RLTAG	7	3.00	4.06	9.10	
XY-FPC-05-CT-8RLTAG	8	3.50	4.56	9.60	
XY-FPC-05-CT-9RLTAG	9	4.00	5.06	10.10	
XY-FPC-05-CT-10RLTAG	10	4.50	5.56	10.60	
XY-FPC-05-CT-11RLTAG	11	5.00	6.06	11.10	5.75
XY-FPC-05-CT-12RLTAG	12	5.50	6.56	11.60	
—	—	—	—	—	
XY-FPC-05-CT-34RLTAG	34	16.50	17.56	22.60	
XY-FPC-05-CT-35RLTAG	35	17.00	18.06	23.10	
XY-FPC-05-CT-36RLTAG	36	17.50	18.56	23.60	
.....		...			
XY-FPC-05-CT-60RLTAG	60	(60-1)*0.5	(60+1)*0.5+0.06	(60+11)*0.5+0.1	



适用线路板(PCB LAYOUT)

序号	品名	材质
1	0.5挂装嵌舌(H2.0)	LCP UL94V-0 本色
2	0.5挂装上装端子(H2.0)	铜合金/表面镀锡
3	0.5挂装跨式后盖(H2.0)	LCP UL94V-0 黑色
4	0.5挂装跨片(H2.0)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~+85°C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 0.5 Pitch 挂装跨式上盖(H=2.0)	
.X±0.3	.X*± 5°	CHK.	Jack	DWG NO. XY-FPC-05-CT-NRLTAG	
.XX±0.2	.X*± 2	DRA	Can	CUSTOMER DRAWING	
.XXX±0.05	.XX*± 1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A