




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
XY-PM254-1-01P-Z-8.5	1	0.00	2.54
XY-PM254-1-02P-Z-8.5	2	2.54	5.08
XY-PM254-1-03P-Z-8.5	3	5.08	7.62
XY-PM254-1-04P-Z-8.5	4	7.62	10.16
XY-PM254-1-05P-Z-8.5	5	10.16	12.70
XY-PM254-1-06P-Z-8.5	6	12.70	15.24
XY-PM254-1-07P-Z-8.5	7	15.24	17.78
XY-PM254-1-08P-Z-8.5	8	17.78	20.32
XY-PM254-1-09P-Z-8.5	9	20.32	22.86
.....			
XY-PM254-1-40P-Z-8.5	40	(PIN-1)X2.54	(PIN)X2.54

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X* ± 5°	APR. Alex	TITLE: 2.54FH H8.5 1xnPin 180# Y# PC3.2 6T			
.XX±0.2	.X* ± 1	CHK. Jack	DWG NO. XY-PM254-1-NP-Z-8.5			
			PROJ. 	CUSTOMER DRAWING		
.XXX±0.1	.XX* ± 0.5	DRA. Can	SIZE A4	SCALE 1:1	SHEET 1 / 1	REV. A