





P/N	PIN	DIM.A	DIM.B
XY-PZ127V-12-01P	2*1	0.00	1.27
XY-PZ127V-12-02P	2*2	1.27	2.54
XY-PZ127V-12-03P	2*3	2.54	3.81
XY-PZ127V-12-04P	2*4	3.81	5.08
XY-PZ127V-12-05P	2*5	5.08	6.35
XY-PZ127V-12-06P	2*6	6.35	7.62
XY-PZ127V-12-07P	2*7	7.62	8.89
XY-PZ127V-12-08P	2*8	8.89	10.16
XY-PZ127V-12-09P	2*9	10.16	11.43
.....			
XY-PZ127V-12-50P	2*50	(PIN-1)x1.27	(PIN)x1.27

SPECIFICATIONS
Current Rating:1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40° to +105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Brass
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR. Alex	TITLE: 1.27PH H1.0 2xnPin 180 W3.4 PC2.3 PA3.9 PB1.0 L7.2 6T		
.XX±0.2	.X*± 1	CHK. Jack	DWG NO. XY-PZ127V-12-NP		
.XXX±0.1	.XX*± 0.5	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1