







SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
XY-PZ200V-12-01P	2*1	0.00	2.00
XY-PZ200V-12-02P	2*2	2.00	4.00
XY-PZ200V-12-03P	2*3	4.00	6.00
XY-PZ200V-12-04P	2*4	6.00	8.00
XY-PZ200V-12-05P	2*5	8.00	10.00
XY-PZ200V-12-06P	2*6	10.00	12.00
XY-PZ200V-12-07P	2*7	12.00	14.00
XY-PZ200V-12-08P	2*8	14.00	16.00
XY-PZ200V-12-09P	2*9	16.00	18.00
.....			
XY-PZ200V-12-40P	2*40	(PIN-1)x2.0	(PIN)x2.0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR.	Alex	TITLE: 2.0PH H2.0 2xnPin 180# PC2.8 PA3.9 PB2.0 L8.7 6T	
.XX±0.25	.X*± 1	CHK.	Jack	DWG NO. XY-PZ200V-12-NP	
.XXX±0.2	.XX*± 0.5	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1