

MATERIAL

1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.

2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.

3.PLATING: GOLD FLASH PLATING OVER NICKEL.

4. SHIELD: BRASS TO .20mm 40u" NICKEL PLATED.

4.3 SHIELD. ELECTRICAL

1.VOLTAGE RATING: 125 VAC RMS.

2.CURRENT RATING: 1.5 AMP.

3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.

4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .

5.DIELECTRIC DIELECTRIC

RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL




1.DURRABILITY: 750 CYCLES MIN.

2.MATING/UNMATING FORCE: 2.24 KG.F MAX.



ENVIRONMENTAL:

1.STORAGE: -40℃~+85℃.

2. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



8	—
7	—
6	RX—
5	—
4	—
3	RX+
2	TX—
1	TX+
PIN	说明



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.35	X.*±3	APR. Alex	TITLE: RJ45 56B雙五線 帶防左接線 DIP			
.XX±0.25	.X.*±2	CHK. Jack	DWG NO. XY-RJ45R56P8			
.XXX±0.15	.XX.*±1*	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A