

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:





Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

Length	1	2	W1	
L	4.0	2.5	13	
Pitch	Position	Rows with Contacts	Contact Arrange	
2.54mm	30	A B C		
	20	A - C		
	10	A - -		
5.08mm	15	A B C		
	10	A - C		
	5	A - -		

9001- 1 7 30 1 C 00 A
Series 1:2.54mm 7:Male Position 1:Dip Length C:Selective 00:G/F A:Tray
2:5.08mm 2:Dip Length Gold Plated Package
W1:Dip Length
W2:Dip Length

公差一览表 TOLERANCE UNLESS OTHERWISE				LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD				
X.	±0.25	X°.	±5°	单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE
.X	±0.20	.X°	±2°	角法 VIEW		设计 DESIGN	LZG	欧式插座 DIN41612 330直针 180度公座
.XX	±0.15	.XX°	±1°	比例 SCALE	1:1	审核 CHKD	FGD	产品料号 PART NO.
.XXX	±0.02	.XXX°	±0.5°	版本 VER	A0	核准 APPD	ZY	LXW254-330-ZZ-G
日期 Date	2009. 04. 15							图号 DRAW NO.
								9001-17301C00A-A0