

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PBT
Max.Processing Temp: 200°C for 30-60seconds
(220°C for 5seconds)

REV.	Q'TY	ECN. NO.		APR.	DATE
P/N		PIN	DIM.A		DIM.B
XY-2.54-2*3P-DC		2*3	5.08		26.92
XY-2.54-2*4P-DC		2*4	7.62		29.46
XY-2.54-2*5P-DC		2*5	10.16		32.00
XY-2.54-2*6P-DC		2*6	12.70		34.54
XY-2.54-2*7P-DC		2*7	15.24		37.08
XY-2.54-2*8P-DC		2*8	17.78		39.60
XY-2.54-2*10P-DC		2*10	22.86		44.70
XY-2.54-2*12P-DC		2*12	27.94		49.78
XY-2.54-2*13P-DC		2*13	30.48		52.30
XY-2.54-2*15P-DC		2*15	35.56		57.40
XY-2.54-2*17P-DC		2*17	40.64		62.50
XY-2.54-2*20P-DC		2*20	48.26		70.10
XY-2.54-2*25P-DC		2*25	60.96		82.85
XY-2.54-2*30P-DC		2*30	73.66		95.40
XY-2.54-2*32P-DC		2*32	78.74		100.48
辛译精密电子有限公司 KinYi Xyconn Electronics Co.,Ltd					
TITLE: 2.54DC2-NP in H17 180# PC3.8 PBT					
DWG NO. XY-2.54-2*NP-DC					
PROJ. 		CUSTOMER DRAWING			
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		

A

B

C

D

E

F

A

B

C

D

E

F

