




SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for 30-60seconds
 (260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ254VS-12-01P	2*1	0.00	2.54
XY-PZ254VS-12-02P	2*2	2.54	5.08
XY-PZ254VS-12-03P	2*3	5.08	7.62
XY-PZ254VS-12-04P	2*4	7.62	10.16
XY-PZ254VS-12-05P	2*5	10.16	12.70
XY-PZ254VS-12-06P	2*6	12.70	15.24
XY-PZ254VS-12-07P	2*7	15.24	17.78
XY-PZ254VS-12-08P	2*8	17.78	20.32
XY-PZ254VS-12-09P	2*9	20.32	22.86
.....
XY-PZ254VS-12-40P	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR. Alex	TITLE: 2.54PH H2.5 2xnPin SMT PC7.5 PA6.0 PB3.2 L11.0 6T	
.X±0.35	X.*± 5°	CHK. Jack	DWG NO. XY-PZ254VS-12-NP	
.XX±0.25	.X*± 1	DRA. Can	CUSTOMER DRAWING	
.XXX±0.2	.XX*± 0.5	PROJ.	SIZE A4	SCALE 1:1
		SHEET 1/1	REV. A	