









RECOMMENDED P.C.B LAYOUT(PCB THICKNESS: 1.6mm)
COMPONENT SIDE VIEW(TOLERANCE: ± 0.05)

**NOTE:****1.MATERIAL:**



- 1.1 HOUSING: LCP, UL 94V-0 COLOR: BLACK.
- 1.2 CONTACT: C2680, T=0.20mm.
- 1.3 SHIELD: C2680, T=0.40mm.
- 1.4 COVER: LCP,UL 94V-0

2.FINISH:

- 2.1 CONTACT: GOLD(1U") PLATING IN CONTACT AREA, 50u"MIN Tin PLATED IN SOLDER AREA,50u" MIN. NICKEL UNDERPLATED OVERALL.
- 2.2 SHIELD: 50u" MIN. NICKEL UNDERPLATED OVERALL.

3.MECHANICAL CHARACTERISTICS

- 3.1 RATING CURRENT: 0.5A
- 3.2 RATING VOLTAGE: 40V
- 3.3 CONTACT RESISTANCE: 40 mΩ MAX
- 3.4 INSULATION RESISTANCE a, UNMATED: 100MΩ MIN AT 500 VDC b, MATED: 10M OHMS MIN AT 150 VDC
- 3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/1MINUTE
- 3.6 DURABILITY: 10000 CYCLES.



SC A-A 1:1

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: DP 20P CONN	
.X ± 0.25	X.* ± 1.5	CHK.	Jack	DWG NO. XY16M-DP20-178	
.XX ± 0.15	.X.* ± 1.0	DRA.	Can	PROJ.	CUSTOMER DRAWING
.XXX ± 0.1	.XX.* $\pm$			SIZE A4	SCALE 1:1
		SHEET	1/1	REV.	A

前空10格

中间装300PCS产品

后空10格

PCS/卷	卷/箱	PCS/箱
300	10	3000

客户使用出料方向

四周角落填充三角垫

纸箱内上下各垫一层纸板

标签

防水袋

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.25	X.*± 1.5
.XX±0.15	.X*± 1.0
.XXX±0.1	.XX*±

APR. Alex	TITLE: DP 20P CONN
CHK. Jack	DWG NO. XY16M-DP20-178
DRA. Can	PROJ. 
SIZE A4	SCALE 1:1

CUSTOMER DRAWING	
SHEET 1/1	REV. A