

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:




Current rating: 2 Amps .

Contact resistance: 20 mΩ initial


Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



Pitch	Position	Rows with Contacts	Contact Arrange
2.54	64	A B	
	32	A -	
5.08	32	A B	
	16	A -	



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

9001-	3	4	64	1	C	00	A
Series	3:2.54mm 2:5.08mm	4:Female	Position	1:Dip Length	C:Selective Gold Plated	00:G/F	A:Tray Package

公差一览表								连兴旺电子(深圳)有限公司			
TOLERANCE UNLESS OTHERWISE				LXWCONN ELECTRONICS (SHENZHEN) CO., LTD							
X.	±0.25	X°	±5°	单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE	欧式插座	DIN41612	
.X	±0.20	.X°	±2°	角法		设计	LZG		264弯 孔	90度母座	
.XX	±0.15	.XX°	±1°	视图 VIEW		设计					
				比例 SCALE	1:1	审核					
.XXX	±0.02	.XXX°	±0.5°	版本 VER	A0	核准	FGD	产品料号 PART NO.	LXW254-264-WK-G		
日期 Date	2009. 04. 15					核准 APPD	ZY	图号 DRAW NO.	9001-34641C00A-A0		