




RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω , Min
Contact Resistance: 20m Ω , Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to $+105^{\circ}$
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240° C for 30-60seconds
(260° C for 5seconds)



P/N	PIN	DIM.A	DIM.B
XY-IDC2.0-2*3P-Z	2*3	4.00	6.00
XY-IDC2.0-2*4P-Z	2*4	6.00	8.00
XY-IDC2.0-2*5P-Z	2*5	8.00	10.00
XY-IDC2.0-2*6P-Z	2*6	10.00	12.00
XY-IDC2.0-2*7P-Z	2*7	12.00	14.00
XY-IDC2.0-2*8P-Z	2*8	14.00	16.00
XY-IDC2.0-2*9P-Z	2*9	16.00	18.00
XY-IDC2.0-2*10P-Z	2*10	18.00	20.00
XY-IDC2.0-2*11P-Z	2*11	20.00	22.00
.....			
XY-IDC2.0-2*35P-Z	2*35	PIN-2.00	PIN

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*±5°	APR.	Alex	TITLE: 2.0DC3-nPin H5.7 180# PC2.8 L8.0 6T	
.XX±0.2	.X*±1	CHK.	Jack	DWG NO. XY-IDC2.0-2*NP-Z	
.XXX±0.1	.XX*±0.5	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1