




Contacts: Copper Alloy

Operating temperature: -55°C TO $+125^{\circ}\text{C}$



Pitch	Position	Rows with Contacts	Contact Arrangement
2.54mm	96	A B C	
	64	A - C	
	32	A - -	
5.08mm	48	A B C	
	32	A - C	
	16	A - -	

(TOP VIEW TOL. :±0.05)

9001-	1	1	64	1	C	00	A
Series	1:2.54mm 2:5.08mm	1:Male	Position	1:Dip Length	C:Selective Gold Plated	00:G/F	A:Tray Package

公差一览表 TOLERANCE UNLESS OTHERWISE				 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD							
X.	±0.25	X°.	±5°	单 位 UNITS	mm	制 图 DRAWING	OD	产品名称 TITLE	欧式插座 DIN41612 364弯 针 90度公座		
.X	±0.20	.X°	±2°	角 法 VIEW		设 计 DESIGN	LZG				
.XX	±0.15	.XX°	±1°	比 例 SCALE	1:1	审 核 CHKD	FGD			产品料号 PART NO.	LXW254-364-WZ-G
.XXX	±0.02	.XXX°	±0.5°	版 本 VER	A0	核 准 APPD	ZY			图 号 DRAW NO.	9001-11641C00A-A0
日期 Date		2009. 04. 15									