



Circuit Diagram



PART NO.	L	Operating force
K3-1336S-F□	2	
K3-1336S-K□	3	250±100gf
K3-1336S-L□	4	

□: 1.Black 2.White

⑤	Contact Spring	—	1	Beryllium copper	Ag Plated	_____
④	Terminal	—	4	Brass Strip	Ag Plated	_____
③	Base	—	1	NYLON	Black	_____
②	Cover	—	1	SUS	Natural	_____
①	KNOB	—	1	NYLON	White	_____
ITEM	PART NAME	TER'NO	QTY	MATERIAL	FINISHING	REMARK

 hro®

							DRAWING	INCHES OR MM	UNIT	DRAWING NO. / DATE			
							CHECKED			TITLE: TOGGLE SWITCHES			
							APPROVALS			PART NO.			
	A	—	NEW	—	—	—	TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	10~30	±0.20	5~10	±0.15	±2°	DRAWING NO.	SHEET 1 OF 1
							~ 5	±0.10					