

SPECIFICATION

MATERIAL:

Housing:PBT+30%G.F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:





Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

Length	1	2	W1	
L	4.0	2.5	13	
Pitch	Position	Rows with Contacts	Contact Arrange	
2.54mm	48	A B C		
	32	A - C		
	16	A - -		
5.08mm	24	A B C		
	16	A - C		
	8	A - -		

9001- 1 7 48 1 C 00 A
Series 1:2.54mm 7:Male Position 1:Dip Length C:Selective 00:G/F A:Tray
2:5.08mm Gold Plated Package
W1:Dip Length
W2:Dip Length

公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS				制图 DRAWING				产品名称 TITLE			
X.	±0.25	X°.	±5°	角法 VIEW	mm	比例 SCALE	1:1	审核 CHKD	FGD	图号 DRAW NO.	9001-17481C00A-A0	欧式插座	DIN41612	348直针	180度公座
.X	±0.20	.X°.	±2°	版本 VER	A0	核准 APPD	ZY	OD	LZG	产品料号 PART NO.	LXW254-348-ZZ-G				
.XX	±0.15	.XX°.	±1°												
.XXX	±0.02	.XXX°.	±0.5°												
日期 Date	2009. 04. 15														



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD