

5	6	7	8
REV.	DATE	ECN NO.	MODIFICATION
A	2018/03/19	/	NEW
			APPROVEP
			Vicky

SPECIFICATIONS:

Voltage Rating:60V DC

Current Rating: 0.3A Max.(Each Pin)

Contact Resistance: 80mΩ MAX





Insulation Resistance: 1000MΩ MIN

Dielectric Withstanding : AC 100V

Operating Temperature : -55°C~+85°C

Contact Material: Copper Alloy,Gold plated,Nickel over all.

Insulator Material: Thermoplastic,UL94V-0 Black.



PIN	10	24	30	34	40	50	60	70	80
A		2.40	3.60	4.40	5.60	7.60	9.60	11.60	13.60
B	1.60	4.40	5.60	6.40	7.60	9.60	11.60	13.60	15.60
C	4.30	7.10	8.30	9.10	10.30	12.30	14.30	16.30	18.30
D	3.20	6.00	7.20	8.00	9.20	11.20	13.20	15.20	17.20
E	2.00	4.80	6.00	6.80	8.00	10.00	12.00	14.00	16.00
2	Housing	1	LCP E6808			Glass:30%		Black	
1	Terminal	N	C5210R-H			Ni 50~90u"UNDERPLATING, GOLD FLASH OVER ALL			
ITEM	Part Name	Q'TY	MATERIAL			FINISH		REMARK	

RECOMMENDED PCB PATTERN DIM.
TOLFRANCF ±0.05

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD

RoHS
Compliant
2013/95/EC

HSF

Pb
RoHS
Compliant

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		Kevin	03/02/15

一般公差 GENERAL TOLERANCE	版本 (REV)
.X ±0.25	A
.XX ±0.20	
.XXX ±0.10	
ANGLES ±0° 30'	

制图 (DR):	Kevin 2016.07.05	品名(TITLE):	0.4mm 2*XP 单槽 母座 合高 H=1.5mm
审核 (CHKD):		料号(PART NO):	LB114-GxxS-WOR
核准 (APPD):		比例(SCALE)	1:1
		单位(UNITS)	mm
		张数(SHEET)	1 OF 1
		图幅(SIZE)	A4