

SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/0.3A AC;
 - 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
 - 3.INSULATION RESISTANCE: 50M Ω MIN;
 - 4.CONTACT RESISTANCE: 100m Ω MAX;
 - 5.OPERATING TEMPERATURE RANGE: -35°C TO 85°C.
- MATERIAL:
- 1.INSULATOR: LCP UL 94V-0 BLACK;
 - 2.TERMINAL: COPPER ALLOY;
 - 3.METAL FITTINGS: COPPER ALLOY.
- PLATING:
- 1.TERMINAL: GOLD PLATING,
NICKEL 50 μ " MIN. OVER ALL;
 - 2.METAL FITTINGS: TIN 100 μ " MIN. OVER NICKEL 50 μ "MIN.

Model	PIN	DIM A	DIM B	DIM C
XY-10DS-DF408C	10	4.50	3.40	1.60
XY-12DS-DF408C	12	4.90	3.80	2.00
XY-16DS-DF408C	16	5.70	4.60	2.80
XY-20DS-DF408C	20	6.50	5.40	3.60
XY-24DS-DF408C	24	7.30	6.20	4.40
XY-30DS-DF408C	30	8.50	7.40	5.60
XY-34DS-DF408C	34	9.30	8.20	6.40
XY-40DS-DF408C	40	10.50	9.40	7.60
XY-50DS-DF408C	50	12.50	11.40	9.60

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X $\pm$ 0.25	X.* $\pm$ 1	APR.	Alex	TITLE: 2x4 SMD TACT SWITCH	
.XX $\pm$ 0.2	.X* $\pm$	CHK.	Jack	DWG NO. XY-NDS-DF408C	
.XXX $\pm$ 0.1	.XX* $\pm$	DRA.	Can	PROJ. 	CUSTOMER DRAWING
		SIZE	A4	SCALE 1:1	SHEET 1/1 REV. A