

SPECIFICATIONS:





- 1.VOLTAGE/CURRENT RATING: 30V/0.3A AC;
- 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
- 3.INSULATION RESISTANCE: 50M Ω MIN;
- 4.CONTACT RESISTANCE: 100m Ω MAX;
- 5.OPERATING TEMPERATURE RANGE: -35°C TO 85°C.

MATERIAL:


- 1.INSULATOR: LCP UL 94V-0 BLACK;
- 2.TERMINAL: COPPER ALLOY;
- 3.METAL FITTINGS: COPPER ALLOY.

PLATING:

- 1.TERMINAL: GOLD PLATING,
NICKEL 50u" MIN. OVER ALL;
- 2.METAL FITTINGS: TIN 100u" MIN. OVER NICKEL 50u"MIN.



Model	PIN	DIM A	DIM B	DIM C
XY-10DP-DF408C	10	3.80	3.20	1.60
XY-12DP-DF408C	12	4.20	3.60	2.00
XY-16DP-DF408C	16	5.00	4.40	2.80
XY-20DP-DF408C	20	5.80	5.20	3.60
XY-24DP-DF408C	24	6.60	6.00	4.40
XY-30DP-DF408C	30	7.80	7.20	5.60
XY-34DP-DF408C	34	8.60	8.00	6.40
XY-40DP-DF408C	40	9.80	9.20	7.60
XY-50DP-DF408C	50	11.80	11.20	9.60



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.25	X.*± 1	APR.	Alex	TITLE: BTB P0.40 HAEDER	
.XX±0.2	.X*±	CHK.	Jack	DWG NO. XY-NDP-DF408C	
.XXX±0.1	.XX*±	DRA	Can	PROJ.	CUSTOMER DRAWING
		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A