

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:


Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



Length	1	2	W1	W2
L	4.0	2.5	13	17
Pitch	Position	Rows with Contacts	Contact Arrange	
2.54	48	A B C		
	32	A - C		
	16	A - -		
5.08	24	A B C		
	16	A - C		
	8	A - -		

PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

9001- 1 6 32 1 C 00 A
Series 1:2.54mm 2:Female Position 1:Dip Length C:Selective 00:G/F A:Tray
2:5.08mm Gold Plated Package

公差一览表 TOLERANCE UNLESS OTHERWISE				LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
X.	±0.25	X°	±5°	单位 UNITS	mm	制图 DRAWING	OD
.X	±0.20	.X°	±2°	角法 VIEW		设计 DESIGN	LZG
.XX	±0.15	.XX°	±1°	比例 SCALE	1:1	审核 CHKD	FGD
.XXX	±0.02	.XXX°	±0.5°	版本 VER	A0	核准 APPD	ZY
日期 Date	2009. 04. 15			产品名称 TITLE	欧式插座 DIN41612 332直孔 180度母座		
图号 DRAW NO.	LXW254-332-ZK-G			产品料号 PART NO.	9001-16321C00A-A0		