


SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω , Min
Contact Resistance: 20m Ω , Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
XY-IDC2.0-2*03P-W	2*3	4.00	6.00
XY-IDC2.0-2*04P-W	2*4	6.00	8.00
XY-IDC2.0-2*05P-W	2*5	8.00	10.00
XY-IDC2.0-2*06P-W	2*6	10.00	12.00
XY-IDC2.0-2*07P-W	2*7	12.00	14.00
XY-IDC2.0-2*08P-W	2*8	14.00	16.00
XY-IDC2.0-2*09P-W	2*9	16.00	18.00
XY-IDC2.0-2*10P-W	2*10	18.00	20.00
XY-IDC2.0-2*11P-W	2*11	20.00	22.00
.....			
XY-IDC2.0-2*35P-W	2*35	PIN-2.00	PIN



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 2.0DC3-nPin H5.7 SMT PC6.9 PB6.2 L8.0 6T	
.XX±0.2	.X*± 1	CHK.	Jack	DWG NO. XY-IDC2.0-2*NP-W	
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ.	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1