







RECOMMENDED PCB LAYOUT
CONNECTOR SIDE

SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/0.3A AC;
 - 2.WITHSTANDING VOLTAGE: 100V AC ONE MINUTE;
 - 3.INSULATION RESISTANCE: 50M Ω MIN;
 - 4.CONTACT RESISTANCE: 100m Ω MAX;
 - 5.OPERATING TEMPERATURE RANGE: - $^{\circ}$ C TO 85 $^{\circ}$ C.
- MATERIAL:
- 1.INSULATOR: LCP UL 94V-0 BLACK;
 - 2.TERMINAL: COPPER ALLOY;
 - 3.METAL FITTINGS: COPPER ALLOY.
- PLATING:
- 1.TERMINAL: GOLD PLATING,
NICKEL 50u" MIN. OVER ALL;
 - 2.METAL FITTINGS: TIN 100u" MIN. OVER NICKEL 50u"MIN.

PIN NO.	10	20	24	26	30	34	40
DIM A	1.60	3.60	4.40	4.80	5.60	6.40	7.60
DIM B	3.40	5.40	6.20	6.60	7.40	8.20	9.40
DIM C	4.50	6.50	7.30	7.70	8.50	9.30	10.50
PIN NO.	44	50	54	60	70	80	
DIM A	8.40	9.60	10.40	11.60	13.60	15.60	
DIM B	10.20	11.40	12.20	13.40	15.40	17.40	
DIM C	11.30	12.50	13.30	14.50	16.50	18.50	

CUSTOMER		连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
一般公差 GENERAL TOLERANCE		制图 (DW):	Kevin	品名(TITLE):	0.4mm BTB SOCKET H1.0
.1 ±0.25 .25 ±0.25 .5 ±0.25 ANGLES ±1°		审核 (CHK):		料号(PART NO):	LB610-GxxS-B0R
版本 (REV): B		比例(SCALE):	1:8	单位(UNITS):	mm
核准 (APP):		张数(SHEET):	1 OF 1	图幅(SIZE):	A4

修订 REV	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE