





Housing:PBT+30%G. F UL94V-0
Contacts:Copper Alloy

ELECTRICAL:

Current rating: 2 Amps .
Contact resistance: 20 mΩ initial
Insulation resistance: 1000 MΩ min @ 500 VDC
Dielectric withstanding voltage:1000 VAC/minute
Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

Pitch	Position	Rows with Contacts	Contact Arrange
2.54mm	48	A B C	
	32	A - C	
	16	A - -	
5.08mm	24	A B C	
	16	A - C	
	8	A - -	

9001-	1	5	48	1	C	00	A
Series	1:2.54mm 2:5.08mm	1:Male	Position	1:Dip Length	C:Selective Gold Plated	00:G/F	A:Tray Package

公差一览表 TOLERANCE UNLESS OTHERWISE				 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD						
X.	±0.25	X°	±5°	单位 UNITS	mm	制图 DRAWING	OD	产品名称 TITLE	欧式插座 348弯 针	DIN41612 90度公座
.X	±0.20	.X°	±2°	角法 VIEW		设计 DESIGN	1ZG			
.XX	±0.15	.XX°	±1°	比例 SCALE	1:1	审核 CHKD	FGD	产品料号 PART NO.	LXW254-348-WZ-G	
.XXX	±0.02	.XXX°	±0.5°							
日期 Date		2009. 04. 15			版本 VER	A0	核准 APP	ZY	图号 DRAW NO	9001-15481C00A-A0