



SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Insulator Material: Polyester (UL 94V-0)
 Contact plating: Gold Flash
 Standard: PBT
 Max. Processing Temp: 200° C for 30-60 seconds
 (220° C for 10 seconds)



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: 2.54DC3-NPin H8.9 180度 PC3.2 L11.5 PBT						
X : ±0.30	X° : ±5°	SIZE	A4	SCALE	N:1	PRODUCT NO.	LXW-BH254V-2-XX	
X.X : ±0.25	X.X° : ±1°	REV	A	UNIT	mm	PROJECT		PAGE 1/1
X.XX : ±0.20	X.XX° : ±0.5°							

CHECKED:	陈超凡	2022/04/25	CHECKED:	/ /	APPROVED:	/ /
----------	-----	------------	----------	-----	-----------	-----

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	5.08	7.62	20	22.86	25.40	36	43.18	45.72
8	7.62	10.16	24	27.94	30.48	40	48.26	50.80
10	10.16	12.70	26	30.48	33.02	44	53.34	55.88
12	12.70	15.24	28	33.02	35.56	50	60.96	63.50
14	15.24	17.78	30	35.56	38.10	60	73.66	76.20
16	17.78	20.32	32	38.10	40.64	64	78.74	81.28
18	20.32	22.86	34	40.64	43.18			