

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:



Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



Length		1	2	W1	W2
L		4.0	2.5	13	17
Pitch	Position	Rows with Contacts	Contact Arrange		
2.54	96	A B C			
	64	A - C			
	32	A - -			
5.08	48	A B C			
	32	A - C			
	16	A - -			

PCB LAYOUT(RECOMMENDED)

(TOP VIEW TOL. :±0.05)

9001- 1 2 64 1 C 00 A
Series 1:2.54mm 2:Female Position 1:Dip Length C:Selective 00:G/F A:Tray
2:5.08mm Gold Plated Package

公差一览表 TOLERANCE UNLESS OTHERWISE				LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
X.	±0.25	X°.	±5°	单位 UNITS	mm	制图 DRAWING	OD
.X	±0.20	.X°.	±2°	角法 VIEW		设计 DESIGN	产品名称 TITLE
.XX	±0.15	.XX°.	±1°	比例 SCALE	1:1	审核 CHKD	图号 PART NO.
.XXX	±0.02	.XXX°.	±0.5°	版本 VER	A0	核准 APPD	图号 DRAW NO.
日期 Date				2009. 04. 15			
				欧式插座 DIN41612 364 直孔 180度母座			
				LXW254-364-ZK-G			
				9001-12641C00A-A0			