

A

B

C

D

E

F

A

B

C

D

E

F

 $A \pm 0.2$ $B \pm 0.08$ $P = 0.40 \pm 0.05$ 0.15 ± 0.02 Vacuum pick up area: $C \pm 0.2$ 2.97 ± 0.2 1.85 ± 0.2

0.10

 1.14 ± 0.15 $H \pm 0.15$

The product is high

 9.60 ± 0.02 0.65 ± 0.02 $P = 0.40 \pm 0.02$ 0.30 ± 0.02 $3.37^{+0.05}_{-0}$ $2.05^{+0}_{-0.05}$ 0.35 ± 0.02 0.23 ± 0.02 RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05


PIN	A	B	C
XY-10DP-DF40C	3.52	1.6	1.0
XY-12DP-DF40C	3.92	2.0	
XY-20DP-DF40C	5.52	3.6	
XY-24DP-DF40C	6.32	4.4	1.2
XY-30DP-DF40C	7.52	5.6	1.5
XY-34DP-DF40C	8.32	6.4	2.3
XY-40DP-DF40C	9.52	7.6	3.2
XY-44DP-DF40C	10.32	8.4	
XY-50DP-DF40C	11.52	9.6	
XY-60DP-DF40C	13.52	11.6	
XY-70DP-DF40C	15.52	13.6	
XY-80DP-DF40C	17.52	15.6	
XY-90DP-DF40C	19.52	17.6	
XY-100DP-DF40C	21.52	19.6	

The product is high

H

XY-XDP-DF40C	1.45
XY-XDP-DF420C	1.95
XY-XDP-DF424C	2.40
XY-XDP-DF429C	2.90
XY-XDP-DF434C	3.40
XY-XDP-DF439C	3.90



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd						
TOLERANCE UNLESS OTHERWISE SPECIFIED								
.X±0.5	X.*± 2	APR. Alex	TITLE: 0.40MM BTB PLUG					
XX±0.35	.X*± 1	CHK. Jack	DWG NO. XY-NDP-DF40C					
XX±0.25	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING			
			SIZE A4	SCALE 1:1	SHEET 1 / 1	REV. A		

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd