

SPECIFICATION

MATERIAL:

Housing:PBT+30%G. F UL94V-0

Contacts:Copper Alloy

ELECTRICAL:





Current rating: 2 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage:1000 VAC/minute

Operating temperature: -55° C TO +125° C



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

Length		1	2	W1	W2
L		4.0	2.5	13	17
Pitch	Position	Rows with Contacts		Contact Arrange	
2.54	44	A B			
	22	A -			
5.08	22	A B			
	11	A -			

9001-	3	6	44	1	C	00	A
Series	3:2.54mm 2:5.08mm	6:Female	Position	1:Dip Length 2:Dip Length W1:Dip Length W2:Dip Length	C:Selective Gold Plated	00:G/F	A:Tray Package

公差一览表 TOLERANCE UNLESS OTHERWISE				LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
X.	±0.25	X°.	±5°	单位 UNITS	mm	制图 DRAWING	OD
.X	±0.20	.X°	±2°	角法 VIEW		设计 DESIGN	LZG
.XX	±0.15	.XX°	±1°	比例 SCALE	1:1	审核 CHKD	FGD
.XXX	±0.02	.XXX°	±0.5°	日期 Date	2009.04.15	版本 VER	A0
				核准 APPD	ZY	图号 DRAW NO.	9001-36441C00A-A0