







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insrlator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)

P/N	PIN	DIM.A	DIM.B
XY-IDC2.54-2*03P-W	2*3	5.08	7.62
XY-IDC2.54-2*04P-W	2*4	7.62	10.16
XY-IDC2.54-2*05P-W	2*5	10.16	12.70
XY-IDC2.54-2*06P-W	2*6	12.70	15.24
XY-IDC2.54-2*07P-W	2*7	15.24	17.78
XY-IDC2.54-2*08P-W	2*8	17.78	20.32
XY-IDC2.54-2*09P-W	2*9	20.32	22.86
XY-IDC2.54-2*10P-W	2*10	22.86	25.40
XY-IDC2.54-2*12P-W	2*12	27.94	30.48
XY-IDC2.54-2*13P-W	2*13	30.48	33.02
XY-IDC2.54-2*14P-W	2*14	33.02	35.56
XY-IDC2.54-2*15P-W	2*15	35.56	38.10
XY-IDC2.54-2*16P-W	2*16	38.10	40.64
XY-IDC2.54-2*17P-W	2*17	40.64	43.18
XY-IDC2.54-2*18P-W	2*18	43.18	45.72
XY-IDC2.54-2*20P-W	2*20	48.26	50.80
XY-IDC2.54-2*22P-W	2*22	53.34	55.88
XY-IDC2.54-2*25P-W	2*25	60.96	63.50
XY-IDC2.54-2*30P-W	2*30	73.66	76.20
XY-IDC2.54-2*32P-W	2*32	78.74	81.28



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54DC3-2XnPin H8.9 90°PC3.2 PB13.3 L15.5-20.5 6T#	
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. XY-IDC2.54-2*NP-W	
.XX±0.2	.X*± 1	PROJ.	Can	CUSTOMER DRAWING	
.XXX±0.1	.XX*± 0.5	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A