






SPECIFICATIONS

- 1.CURRENT RATING: 0.3A .
- 2.VOLTAGE RATING 30V AC/DC.
- 3.TEMPERATURE RANGE:-35°C TO +85°C
- 4.CONTACT RESISTANCE: 90mΩ MAX.
- 5.INSULATION RESISTANCE: 50 MΩ MIN.
- 6.WITHSTANDING VOLTAGE: 100V AC/MINUTE.



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

PIN	A	B	C
XY-10DS-DF40C	4.6	1.6	1.0
XY-12DS-DF40C	5.0	2.0	
XY-20DS-DF40C	6.6	3.6	
XY-24DS-DF40C	7.4	4.4	1.2
XY-30DS-DF40C	8.6	5.6	1.5
XY-34DS-DF40C	9.4	6.4	2.3
XY-40DS-DF40C	10.6	7.6	3.2
XY-50DS-DF40C	12.6	9.6	
XY-60DS-DF40C	14.6	11.6	
XY-70DS-DF40C	16.6	13.6	
XY-80DS-DF40C	18.6	15.6	
XY-90DS-DF40C	20.6	17.6	
XY-100DS-DF40C	22.6	19.6	

The product is high	H
XY-XDS-DF40C	1.45
XY-XDS-DF420C	1.95
XY-XDS-DF240C	2.40
XY-XDS-DF429C	2.90
XY-XDS-DF434C	3.40
XY-XDS-DF439C	3.90

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*± 2	APR. Alex	TITLE: 0.40MM BTB SOCKET		
.XX±0.35	.X*± 1	CHK. Jack	DWG NO. XY-NDS-DF40C		
.XXX±0.25	.XX*±	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1 / 1