









RoHS
REACH



A	H (高度)
Ø3.50	4.3~5
Ø3.45	5.5
Ø3.35	6
Ø3.20	6.5
Ø3.10	7
Ø3.00	7.5
Ø3.00	8~29



电路图

序号	产品名称	材料规格	表面处理	颜色	数量	性能	未注尺寸公差 (mm)	设计	陈建明	图面	图框	产品名称: 轻触开关
1	按钮	PPA/21以上聚碳柄			1	额定规格	DC12V/50mA		臧志杨	单位	A4	产品规格: TS-6645DD6x6x*-250
2	盖板	铁			1	接触电阻	≤100mΩ	.X	±0.20	比例	MM	
3	弹片	高精铜	复	银	1	绝缘电阻	≥100MΩ	.XX	±0.10	重量		
3	弹片	不锈钢			1	耐电压	AC250V/min			页码	1/1	
4	基座	PPA			1	动作力	100/180/250g	.XXX	±0.01	版次	A/0	浙江创都电子科技有限公司
5	接线片	铜	镀	银	1				吴建敏			
									吴丹			