








Rev.	ECN	Number	Description	Date	Drawn	Checkd	Approved



焊盘尺寸

尺寸公差 ±0.05

技术要求:

1.材质:不锈钢SUS301,T=0.15±0.005;

2.端子锡脚焊接面和接触面不可有毛边,其他部位毛边最大0.03m

3.扭曲:45°/1000mm,拱形 5mm/1000mm;

4.标示有“▼”符号的为重点控制和检验尺寸;

5.未标注之R MAX R0.13;

6.电镀须满足24小时盐雾测试;

7.寿命测试>2万次,产品弹力要求在60gf~80gf之间

8.镍底50~80u”min,产品外表面镀锡80~100U”MIN

TITLE
客户图
RF CABLE(ø1.13) CAN CLIP
L2.9*W1.54*H1.63

GENERAL TOLERANCE

XX. ±0.50

X. ±0.35

.X ±0.25

.XX ±0.15

X.° ±2.0°

.X° ±1.0°

.XX° ±0.5°

SCALE:


1:1

UNIT:

mm

SIZE:

A4



DRAWN

CHECK

APPROVE

DATE

DATE

DATE

DWG. NO.

681-0075A-01

PARTS NO.(INTENDED USE)

0075A1

深圳市金航标电子有限公司

KH-PBJ-29154163

www.kinghelm.com.cn

0755-28190160

REV.

A

SHEET

1/2