







TS-B001-F



电 路 图



PCB. 焊接图

- 主要技术规格:
- 额定值: 50mA DC12V
 - 接触电阻: ≤100mΩ
 - 操作力: 250±30gf
 - 行程: 0.25±0.1mm
 - 绝缘电阻: 100MΩ
 - 抗电强度: 250V 50HZ 1Min.
 - 寿命: 100,000 Cycles

材料:

本体:	LCP	(白色)
按钮:	PPA	(黑色)
卡件:	黄铜	(镀银)
弹片:	不锈钢	(镀银)
盖板:	黄铜	(镀锡锑)

浙江创都电子科技有限公司

第一视角



标记	处数	更改文件号	签 名	日 期	比 例	mm	一般公差	
设计	陈建明	2011.05.08	单 位	mm	>0.5~2	±0.10		
审 核	臧志杨	2011.05.10	重 量		>2~5	±0.25		
批 准	吴建敏	2011.05.14			>5~10	±0.30	角度	±0.5°

名称: 轻触开关

型号: TS-1101U**-3x6x**-260