






Kinghelm®

φ0.90吸嘴位置



焊盘尺寸

尺寸公差 ±0.05

技术要求:

1.材质:不锈钢SUS301,T=0.15±0.005;

2.端子锡脚焊接面和接触面不可有毛边,其他部位毛边最大0.03mm;

3.扭曲:45°/1000mm,拱形 5mm/1000mm;


4.标示有“▼”符号的为重点控制和检验尺寸;

5.未标注之R MAX R0.13;

6.电镀须满足24小时盐雾测试;

7.寿命测试>2万次,产品弹力要求在60gf~80gf之间

8.镍底50~80u"min,产品外表面镀锡80~100U"MIN



3D 图

TITLE

客户图

RF CABLE(φ0.81) CAN CLIP
L2.1*W1.20*H1.30

GENERAL TOLERANCE

XX. ±0.50

X. ±0.35

.X ±0.25

.XX ±0.15

X.° ±2.0°

.X° ±1.0°

.XX° ±0.5°

SCALE:


1:1

UNIT:

mm

SIZE:

A4



DRAWN

CHECK

APPROVE

DATE

DATE

DATE

DWG. NO.

681-0074B-01

PARTS NO.(INTENDED USE)

0074B1

深圳市金航标电子有限公司

KH-PBJ-211213

www.kinghelm.com.cn

0755-28190160

REV.

A

SHEET

1/1