







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
PZ2.54-US2S-01A-R	2*1	0.00	2.54
PZ2.54-US2S-02A-R	2*2	2.54	5.08
PZ2.54-US2S-03A-R	2*3	5.08	7.62
PZ2.54-US2S-04A-R	2*4	7.62	10.16
PZ2.54-US2S-05A-R	2*5	10.16	12.70
PZ2.54-US2S-06A-R	2*6	12.70	15.24
PZ2.54-US2S-07A-R	2*7	15.24	17.78
PZ2.54-US2S-08A-R	2*8	17.78	20.32
PZ2.54-US2S-09A-R	2*9	20.32	22.86
.....			
PZ2.54-US2S-40A-R	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 2.54PH H2.5 2xnPin SMT PC7.5 PA6.0 PB3.2 L11.0 6T			
.XX±0.2	.X*± 3°	CHK.	Jack	DWG NO. PZ2.54-US2S-NA-R			
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A